

Insulated Panels
UK & Ireland



Protected by



QuadCore® KS1000RW Wall Panel Product Data Sheet

POWERED BY
QuadCore®
TECHNOLOGY



Product Data


Applications

QuadCore® KS1000RW Wall Panels are through-fix, trapezoidal profiled, insulated wall panels which can be used in both horizontal and vertical orientation.

Available Lengths

Standard Lengths (m)	1.8 - 14.5
Longer Lengths (non-standard) (m)	14.5 - 29.2
Shorter Lengths (non-standard) (m)	Below 1.8

Note: Additional costs and transport restrictions may apply for non-standard lengths. All lengths may change for export (outside of the UK and Ireland).



Dimensions, Weight & Thermal Performance

Core Thickness (mm)	40	53	60	73	80	91	100	115	120	137	150	167
Overall Thickness (mm)	71	84	91	104	111	122	131	146	151	168	181	198
U-Value (W/m²K)	0.47	0.35	0.31	0.25	0.23	0.20	0.18	0.16	0.15	0.13	0.12	0.11
Weight (kg/m²)	9.0	9.5	9.7	10.2	10.5	10.9	11.3	11.8	12.0	12.7	13.2	13.8

The QuadCore® insulation used in QuadCore® KS1000RW Wall Panels has a Thermal Conductivity (λ) of 0.018 W/m.K
QuadCore® KS1000RW Wall Panels have a Thermal Transmittance (U-Value), calculated using the method required by the Building Regulations Part L2 (England & Wales), Building Standards Section 6 (Scotland), Part L (Republic of Ireland) and Part F2 (Northern Ireland).

Insulation Core

QuadCore® KS1000RW Wall Panels are manufactured with an HCFC, CFC and HFC free QuadCore® insulation core.



Certification and Testing

Reaction to Fire

QuadCore® KS1000RW Wall Panels are classified B-s1,d0, when tested on the internal face of the product, according to the European Reaction to Fire classification system (Euroclasses) BS EN 13501-1: 2018 under the certified name QuadCore® KS1000RW when using the following internal liners:

- CLEANsafe 15, CLEANsafe 25, CLEANsafe 55, CLEANsafe 120 and AQUAsafe 55.

Please contact Kingspan Tech-eXchange for information relating to the external face.

Fire Resistance

Fire resistance classifications are subject to panel thickness, orientation, method of assembly, and steel coating. Please contact Kingspan Tech-eXchange for project specific details.

Insurer Approvals

QuadCore® KS1000RW Wall Panels are tested to:

- LPS 1181 Part 1: Issue 1.2 Requirements and tests for builtup cladding and sandwich panel systems for use as the external envelope of buildings certified to:
 - LPS 1181-1 Grade EXT-B under the certified name QuadCore® KS1000RW (Wall Panel) for thicknesses 40 - 150 mm and vertical orientation.
 - LPS 1181-1 Grade EXT-A15 under the certified name QuadCore® KS1000RW (Wall Panel) for thicknesses 40 - 150 mm and vertical orientation.
 - LPS 1181-1 Grade EXT-A30 under the certified name QuadCore® KS1000RW (Wall Panel) for thicknesses 80 - 150 mm and vertical orientation.
- FM 4880 approval standard for class 1 fire rating of building panels or interior finish materials under the certified name KS1000RW for thicknesses 40 - 167 mm.
- FM 4881 approval standard for class 1 exterior wall systems under the certified name KS1000RW for thicknesses 40 - 167 mm.
- FM 4882 approval standard for class 1 interior wall and ceiling materials or systems for smoke sensitive occupancies under the certified name KS1000RW for thicknesses 40 - 167 mm.

Insurer approvals are large scale testing regimes that provide objective third-party testing, which is underpinned by quarterly, bi-annual and annual factory surveillance audits (depending on the region) to verify compliance. Insurer approvals are subject to panel thickness, cover width, orientation, method of assembly, steel coating and manufacturing facility. Please contact Kingspan Tech-eXchange for further information.



LPS 1181-1: Issue 1.2
Cert: 186f & 260f
LPCB Ref: 186f/04 & 260f/04



LPS 1181-1: Issue 1.2
Cert: 186f & 260f
LPCB Ref: 186f/05 & 260f/05



LPS 1181-1: Issue 1.2
Cert: 186f & 260f
LPCB Ref: 186f/06 & 260f/06

Environmental

Kingspan Insulated Panels produced in the UK and Ireland are certified to BES 6001 (Framework Standard for the Responsible Sourcing of Construction Products) 'Good'. QuadCore® Insulated Panel systems have Environmental Product Declarations in accordance with the requirements of EN 15804 + A2: 2019.

In addition, facilities located in Kingscourt, Holywell and Sherburn generate renewable energy onsite which contributes to that sites energy mix.

Recycled content calculations are available for all QuadCore® products via technical services. Kingspan insulated panels can directly contribute to BREEAM® / LEED® credits.

Air Leakage

An air leakage rate of 3m³/hr/m² at 50Pa or less can be achieved when using Kingspan insulated roof and wall panels.

For information on detailing required to achieve lower air leakage rates please contact Kingspan Tech-eXchange.

Acoustic

Sound Reduction Index (SRI)

Frequency (Hz)	63	125	250	500	1000	2000	4000	8000
SRI (dB)	20	18	20	24	20	29	39	47

QuadCore® KS1000RW Wall Panels have a single figure weighted sound reduction $R_w = 25\text{dB}$. Results are based on panels of similar profile and core material.

Product Data

Materials

Substrate

Metallic protected steel to BS EN 10346: 2015.

Please contact Kingspan Tech-eXchange for information on other substrates.

Coatings – External Weather Sheet

- Kingspan XL Forté: Consists of a multi-layer organic coating, embossed with a traditional leather-grain finish.
- Kingspan Spectrum: Consists of a coated semi-gloss finish with slight granular effect.

The Kingspan XL Forté range is not suitable for external wall applications above 18m in height. For more information please contact Kingspan Tech-eXchange.

For Reaction to Fire performance of external weather sheets please contact Kingspan Tech-eXchange.

Coatings – Internal Liner Sheet

- Kingspan CLEANsafe 15: The coating has been developed for use as the internal lining of insulated panels. Standard colour is “bright white” with an easily cleaned surface.
- Kingspan CLEANsafe 120: The coating has been developed for use as the internal lining of insulated panels where a high level of cleanliness and hygiene is required, and the panels are to be cleaned down on a regular basis.
- Kingspan AQUAsafe 55: The coating has been developed for use as the internal lining of insulated panels to swimming pool internal environments.

For Reaction to Fire performance of panels with above internal liners please see Certification and Testing section.

Panel End Cut Back

Standard Cut Back	20 mm
End Lap Vertical	100 mm
End Lap Horizontal	50 mm
Cut Back Horizontal (vertical top hat)	20 mm

For further information in relation to end laps please contact Kingspan Tech-eXchange.

Product Tolerances

Cut to Length	± 5 mm
Cover Width	± 2 mm
Thickness (Core ≤ 100 mm)	± 2 mm
Thickness (Core > 100 mm)	± 2%
End Square	± 3 mm

Seals

An optional factory applied weather seal (FAWS) can be supplied by Kingspan on request (this must be specified at order stage and is subject to additional charge).

Handing

QuadCore® KS1000RW Wall Panels can be manufactured in both left to right handed (LH) and right to left handed (RH).

Quality & Durability

QuadCore® KS1000RW Wall Panels are manufactured from the highest quality materials, using state of the art production equipment to rigorous quality control standards, complying with BS EN ISO 9001 standard, ensuring long term reliability and service life. The panels are also being manufactured under Environmental Management System Certification BS EN ISO 14001, Energy Management System Certification BS EN ISO 50001 and Occupational Health and Safety Certification BS EN ISO 45001 and Compliance Management Systems BS EN ISO 37301.

QuadCore® KS1000RW Wall Panels are CE marked to BS EN 14509: 2013.



Warranty

QuadCore® Assured Panel Warranty

- 25 years insurance backed thermal performance
- 25 years insurance backed fire performance
- 25 years structural performance
- 25 years environmental performance
- Up to 40 years coating performance

QuadCore® Assured System Warranty

- 25 years insurance backed thermal performance
- 25 years insurance backed fire performance
- 25 years structural performance
- 25 years environmental performance
- Up to 40 years coating performance
- 25 years warranty on system accessories*

*Please contact Kingspan Tech-eXchange or refer to the 'QuadCore® Assured' brochure for a list of accessories covered by Kingspan.

Packing

QuadCore® KS1000RW Wall Panels are stacked weather sheet to weather sheet (to minimise pack height). The top and sides are protected by either cardboard or polystyrene and spiral wrap stretch polyfilm. The number of panels in a pack will vary depending on thickness.

Core Thickness (mm)	40	53	60	73-80	91-100	115-120	137-167
No. of Panels per Pack	17	15	13	11	9	8	6

Note: Applies to UK pack sizes. Please contact Kingspan Tech-eXchange for export information.

Sea Freight

Fully timber crated packs are available on projects requiring delivery by sea freight shipping, at additional costs. Alternatively, steel containers can be used. Special loading charges apply.

Delivery

All deliveries (unless indicated otherwise) are by road transport to project site. Off-loading is the responsibility of the client.

Site Installation Procedure

Site assembly instructions are available from Kingspan Tech-eXchange.

Product Data: Load / Span Tables

Load / span tables to be compared against calculated characteristic (i.e. unfactored) wind load values.

Single Span

Core Thickness (mm)	Load Type	Uniformly distributed imposed load (kN/m²)																																
		Span (m)																																
		0.6	0.8	1.0	1.2	1.4	1.6	1.8	2.0	2.2	2.4	2.6	2.8	3.0	3.2	3.4	3.6	3.8	4.0	4.2	4.4	4.6	4.8	5.0	5.2	5.4	5.6	5.8	6.0	6.2	6.4	6.6	6.8	7.0
40	Pressure	12.60	7.91	5.63	4.31	3.46	2.85	2.40	2.05	1.77	1.55	1.36	1.21	1.08	0.97	0.87	0.79	0.72	0.65	0.60	0.55	0.51	0.47	-	-	-	-	-	-	-	-	-	-	-
	Suction	12.21	7.51	5.27	3.98	3.16	2.59	2.17	1.85	1.59	1.39	1.22	1.08	0.96	0.86	0.78	0.70	0.64	0.58	0.53	0.49	0.39	0.32	-	-	-	-	-	-	-	-	-	-	-
53	Pressure	13.27	8.78	6.46	5.10	4.20	3.54	3.04	2.64	2.32	2.04	1.82	1.62	1.46	1.31	1.19	1.08	0.99	0.90	0.83	0.77	0.71	0.66	0.61	0.57	0.53	0.49	-	-	-	-	-	-	-
	Suction	13.09	8.36	6.08	4.75	3.88	3.26	2.79	2.41	2.11	1.86	1.65	1.48	1.32	1.19	1.08	0.98	0.90	0.82	0.75	0.69	0.63	0.58	0.53	0.46	0.39	0.32	-	-	-	-	-	-	-
60	Pressure	13.63	9.25	6.92	5.54	4.61	3.93	3.40	2.97	2.62	2.33	2.08	1.86	1.68	1.52	1.38	1.25	1.15	1.05	0.97	0.89	0.82	0.76	0.71	0.66	0.62	0.58	0.54	0.49	-	-	-	-	-
	Suction	13.57	8.83	6.53	5.18	4.28	3.63	3.14	2.74	2.41	2.14	1.90	1.71	1.54	1.39	1.26	1.15	1.03	0.92	0.83	0.76	0.69	0.63	0.58	0.54	0.50	0.46	0.40	0.33	-	-	-	-	-
73	Pressure	14.30	9.83	7.54	6.16	5.22	4.52	3.96	3.50	3.11	2.78	2.50	2.25	2.04	1.85	1.68	1.54	1.41	1.30	1.19	1.10	1.02	0.95	0.88	0.82	0.77	0.72	0.68	0.64	0.60	0.56	0.52	0.48	-
	Suction	14.30	9.70	7.37	5.99	5.05	4.36	3.81	3.36	2.99	2.67	2.40	2.16	1.95	1.71	1.50	1.34	1.19	1.07	0.97	0.88	0.80	0.74	0.68	0.63	0.58	0.54	0.50	0.47	0.44	0.41	0.39	0.34	-
80	Pressure	14.63	10.07	7.81	6.45	5.51	4.80	4.23	3.76	3.35	3.01	2.71	2.45	2.22	2.02	1.84	1.68	1.54	1.42	1.31	1.21	1.12	1.04	0.97	0.91	0.85	0.79	0.75	0.70	0.66	0.62	0.59	0.55	0.51
	Suction	14.66	10.18	7.83	6.43	5.47	4.75	4.18	3.71	3.31	2.97	2.67	2.41	2.10	1.84	1.62	1.44	1.29	1.16	1.05	0.95	0.87	0.80	0.73	0.68	0.63	0.58	0.54	0.51	0.47	0.44	0.42	0.39	0.37
91	Pressure	15.05	10.57	8.34	6.98	6.03	5.30	4.70	4.20	3.77	3.40	3.07	2.78	2.53	2.30	2.10	1.93	1.77	1.63	1.51	1.40	1.30	1.20	1.12	1.05	0.98	0.91	0.85	0.79	0.74	0.70	0.66	0.62	0.58
	Suction	15.23	10.93	8.57	7.14	6.15	5.39	4.78	4.26	3.83	3.44	3.11	2.66	2.30	2.01	1.77	1.57	1.41	1.27	1.15	1.04	0.95	0.87	0.80	0.74	0.69	0.64	0.59	0.55	0.52	0.49	0.46	0.43	0.41
100	Pressure	15.38	10.96	8.75	7.40	6.44	5.70	5.08	4.56	4.10	3.71	3.36	3.05	2.78	2.53	2.32	2.13	1.96	1.80	1.67	1.55	1.43	1.34	1.24	1.15	1.07	0.99	0.92	0.86	0.81	0.76	0.71	0.67	0.63
	Suction	15.51	11.55	9.17	7.72	6.65	5.82	5.17	4.65	4.23	3.84	3.32	2.84	2.46	2.15	1.90	1.68	1.51	1.36	1.23	1.12	1.02	0.93	0.86	0.79	0.74	0.68	0.64	0.59	0.56	0.52	0.49	0.46	0.44
115	Pressure	15.51	11.58	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.32	3.10	2.91	2.67	2.45	2.26	2.08	1.93	1.79	1.66	1.54	1.41	1.31	1.21	1.12	1.05	0.98	0.92	0.86	0.81	0.76	0.72
	Suction	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.13	2.71	2.37	2.09	1.86	1.67	1.50	1.36	1.24	1.13	1.04	0.95	0.88	0.82	0.76	0.71	0.66	0.62	0.58	0.54	0.51	0.48
120	Pressure	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.32	3.10	2.91	2.74	2.55	2.35	2.17	2.01	1.87	1.74	1.60	1.47	1.36	1.26	1.17	1.09	1.02	0.95	0.89	0.84	0.79	0.74
	Suction	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.23	2.80	2.45	2.16	1.92	1.72	1.55	1.40	1.27	1.16	1.07	0.98	0.91	0.84	0.78	0.73	0.68	0.64	0.60	0.56	0.53	0.50
137	Pressure	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.32	3.10	2.91	2.74	2.59	2.45	2.33	2.22	2.12	1.96	1.80	1.66	1.53	1.42	1.32	1.23	1.15	1.07	1.01	0.95	0.89	0.84
	Suction	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.32	3.07	2.68	2.37	2.11	1.89	1.70	1.54	1.40	1.28	1.17	1.08	1.00	0.92	0.86	0.80	0.75	0.70	0.66	0.62	0.58	0.55
150	Pressure	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.32	3.10	2.91	2.74	2.59	2.45	2.33	2.22	2.12	2.02	1.94	1.80	1.67	1.54	1.44	1.34	1.25	1.17	1.10	1.03	0.97	0.92
	Suction	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.32	3.10	2.86	2.52	2.24	2.01	1.81	1.64	1.49	1.36	1.25	1.15	1.06	0.99	0.92	0.85	0.80	0.75	0.70	0.66	0.62	0.58
167	Pressure	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.32	3.10	2.91	2.74	2.59	2.45	2.33	2.22	2.12	2.02	1.94	1.86	1.79	1.71	1.59	1.48	1.38	1.29	1.21	1.14	1.07	1.01
	Suction	15.51	11.63	9.31	7.76	6.65	5.82	5.17	4.65	4.23	3.88	3.58	3.32	3.10	2.91	2.71	2.41	2.16	1.95	1.76	1.60	1.47	1.34	1.24	1.14	1.06	0.99	0.92	0.86	0.80	0.75	0.71	0.67	0.63

- Values have been calculated using the method described in BS EN 14509: 2013, for dark coloured panels.
- The following deflection limits have been used:
 - Short term pressure loading $L/100$.
 - Short term suction loading $L/100$.
- All panel thicknesses have been calculated with a minimum end support width of 50 mm and intermediate support width of 50 mm. Larger support widths are possible.

- The actual wind suction resisted by the panel is dependent upon the number of fasteners and the material of the supporting element.
- The fastener calculation should be carried out in accordance with the appropriate standards.
- For intermediate values linear interpolation may be used.
- The allowable steelwork tolerance between bearing planes of adjacent supports is ± 5 mm.

Product Data: Load / Span Tables

Load / span tables to be compared against calculated characteristic (i.e. unfactored) wind load values.

Double Span

Core Thickness (mm)	Load Type	Uniformly distributed imposed load (kN/m²)																																
		Span (m)																																
		0.6	0.8	1.0	1.2	1.4	1.6	1.8	2.0	2.2	2.4	2.6	2.8	3.0	3.2	3.4	3.6	3.8	4.0	4.2	4.4	4.6	4.8	5.0	5.2	5.4	5.6	5.8	6.0	6.2	6.4	6.6	6.8	7.0
40	Pressure	10.02	7.50	5.63	4.31	3.46	2.85	2.40	2.05	1.76	1.52	1.33	1.18	1.05	0.95	0.86	0.78	0.72	0.65	0.60	0.55	0.51	0.47	0.43	0.39	0.36	0.33	-	-	-	-	-	-	-
	Suction	9.59	7.14	5.27	3.98	3.16	2.59	2.17	1.81	1.54	1.33	1.16	1.03	0.91	0.82	0.74	0.68	0.62	0.57	0.53	0.49	0.45	0.42	0.39	0.36	0.34	0.31	-	-	-	-	-	-	-
53	Pressure	11.01	8.25	6.46	5.10	4.10	3.29	2.71	2.29	1.96	1.71	1.51	1.34	1.21	1.09	0.99	0.91	0.83	0.77	0.71	0.66	0.62	0.57	0.51	0.46	0.42	0.39	0.35	0.32	-	-	-	-	-
	Suction	10.56	7.86	6.08	4.75	3.70	2.93	2.40	2.01	1.72	1.49	1.31	1.16	1.04	0.94	0.86	0.78	0.72	0.66	0.62	0.57	0.53	0.50	0.47	0.44	0.42	0.39	0.37	0.35	-	-	-	-	-
60	Pressure	11.54	8.66	6.92	5.51	4.27	3.43	2.84	2.40	2.07	1.81	1.60	1.43	1.28	1.16	1.06	0.97	0.89	0.83	0.77	0.71	0.67	0.62	0.56	0.51	0.46	0.42	0.38	0.35	0.32	-	-	-	-
	Suction	11.09	8.26	6.53	5.04	3.85	3.06	2.51	2.11	1.81	1.57	1.39	1.24	1.11	1.00	0.91	0.84	0.77	0.71	0.66	0.62	0.58	0.54	0.51	0.48	0.45	0.43	0.40	0.38	0.36	-	-	-	-
73	Pressure	12.55	9.42	7.54	5.84	4.56	3.69	3.07	2.61	2.26	1.98	1.76	1.57	1.42	1.29	1.18	1.08	1.00	0.93	0.86	0.80	0.75	0.71	0.65	0.59	0.53	0.48	0.44	0.40	0.37	0.34	0.31	-	-
	Suction	12.09	9.01	7.18	5.36	4.13	3.30	2.72	2.30	1.98	1.73	1.53	1.36	1.23	1.11	1.02	0.93	0.86	0.80	0.74	0.69	0.65	0.61	0.57	0.54	0.51	0.49	0.46	0.44	0.42	0.40	0.38	-	-
80	Pressure	13.09	9.84	7.81	6.01	4.71	3.83	3.20	2.72	2.36	2.07	1.84	1.65	1.49	1.35	1.24	1.14	1.05	0.98	0.91	0.85	0.80	0.75	0.70	0.63	0.57	0.52	0.47	0.43	0.39	0.36	0.33	0.31	-
	Suction	12.63	9.42	7.51	5.53	4.27	3.43	2.84	2.40	2.07	1.81	1.60	1.43	1.29	1.17	1.07	0.98	0.91	0.84	0.78	0.73	0.69	0.65	0.61	0.57	0.54	0.52	0.49	0.47	0.44	0.42	0.41	0.39	-
91	Pressure	13.95	10.50	8.34	6.28	4.94	4.03	3.38	2.89	2.51	2.21	1.96	1.76	1.59	1.45	1.33	1.23	1.13	1.05	0.98	0.92	0.86	0.81	0.76	0.72	0.68	0.63	0.58	0.53	0.49	0.45	0.42	0.39	0.36
	Suction	13.48	10.07	7.85	5.79	4.49	3.62	3.01	2.55	2.20	1.93	1.71	1.53	1.38	1.26	1.15	1.06	0.98	0.91	0.85	0.79	0.74	0.70	0.66	0.62	0.59	0.56	0.53	0.51	0.48	0.46	0.44	0.42	0.41
100	Pressure	14.38	10.83	8.62	6.49	5.13	4.20	3.53	3.02	2.63	2.31	2.06	1.85	1.68	1.53	1.40	1.29	1.20	1.11	1.04	0.97	0.91	0.86	0.81	0.77	0.73	0.69	0.66	0.61	0.56	0.52	0.48	0.45	0.42
	Suction	13.91	10.39	8.09	5.99	4.67	3.78	3.14	2.67	2.31	2.02	1.79	1.61	1.45	1.32	1.21	1.12	1.03	0.96	0.90	0.84	0.79	0.74	0.70	0.66	0.63	0.60	0.57	0.54	0.52	0.49	0.47	0.45	0.43
115	Pressure	14.43	10.88	8.73	6.82	5.43	4.46	3.76	3.23	2.82	2.49	2.22	2.00	1.81	1.65	1.52	1.40	1.30	1.21	1.13	1.06	0.99	0.94	0.89	0.84	0.79	0.76	0.72	0.69	0.65	0.63	0.60	0.56	0.52
	Suction	13.96	10.44	8.32	6.32	4.96	4.03	3.36	2.86	2.48	2.18	1.93	1.74	1.57	1.43	1.31	1.21	1.12	1.04	0.97	0.91	0.86	0.81	0.76	0.72	0.69	0.65	0.62	0.59	0.57	0.54	0.52	0.50	0.48
120	Pressure	14.45	10.90	8.74	6.93	5.52	4.55	3.84	3.30	2.88	2.54	2.27	2.04	1.85	1.69	1.56	1.44	1.33	1.24	1.16	1.09	1.02	0.96	0.91	0.86	0.82	0.78	0.74	0.70	0.67	0.64	0.62	0.59	0.56
	Suction	13.97	10.45	8.33	6.43	5.05	4.11	3.43	2.93	2.54	2.23	1.98	1.78	1.61	1.47	1.34	1.24	1.15	1.07	1.00	0.94	0.88	0.83	0.78	0.74	0.71	0.67	0.64	0.61	0.58	0.56	0.53	0.51	0.49
137	Pressure	14.51	10.95	8.79	7.30	5.84	4.83	4.09	3.52	3.08	2.73	2.44	2.20	2.00	1.82	1.68	1.55	1.44	1.34	1.25	1.18	1.11	1.04	0.99	0.94	0.89	0.84	0.81	0.77	0.73	0.70	0.67	0.65	0.62
	Suction	14.03	10.50	8.37	6.79	5.36	4.38	3.67	3.14	2.72	2.40	2.13	1.91	1.73	1.58	1.45	1.34	1.24	1.16	1.08	1.01	0.95	0.90	0.85	0.81	0.77	0.73	0.70	0.66	0.64	0.61	0.58	0.56	0.54
150	Pressure	14.55	10.99	8.82	7.36	6.08	5.04	4.27	3.69	3.23	2.86	2.56	2.31	2.10	1.92	1.77	1.63	1.52	1.41	1.32	1.24	1.17	1.10	1.04	0.99	0.94	0.89	0.85	0.81	0.78	0.75	0.72	0.69	0.66
	Suction	14.07	10.53	8.39	6.96	5.59	4.58	3.85	3.29	2.86	2.52	2.24	2.02	1.83	1.67	1.53	1.41	1.31	1.22	1.14	1.07	1.01	0.95	0.90	0.85	0.81	0.77	0.74	0.70	0.67	0.65	0.62	0.59	0.57
167	Pressure	14.60	11.03	8.86	7.39	6.32	5.30	4.50	3.90	3.42	3.03	2.71	2.45	2.23	2.04	1.88	1.74	1.62	1.51	1.41	1.33	1.25	1.18	1.12	1.06	1.01	0.96	0.91	0.87	0.83	0.80	0.77	0.74	0.71
	Suction	14.12	10.57	8.43	6.98	5.88	4.84	4.07	3.49	3.04	2.68	2.38	2.14	1.94	1.77	1.63	1.50	1.40	1.30	1.22	1.14	1.08	1.02	0.96	0.91	0.87	0.83	0.79	0.75	0.72	0.69	0.66	0.64	0.61

- Values have been calculated using the method described in BS EN 14509: 2013, for dark coloured panels.
- The following deflection limits have been used:
 - Short term pressure loading $L/100$.
 - Short term suction loading $L/100$.
- All panel thicknesses have been calculated with a minimum end support width of 50 mm and intermediate support width of 50 mm. Larger support widths are possible.

- The actual wind suction resisted by the panel is dependent upon the number of fasteners and the material of the supporting element.
- The fastener calculation should be carried out in accordance with the appropriate standards.
- For intermediate values linear interpolation may be used.
- The allowable steelwork tolerance between bearing planes of adjacent supports is ± 5 mm.

Product Data: Load / Span Tables

Load / span tables to be compared against calculated characteristic (i.e. unfactored) wind load values.

Triple Span

Core Thickness (mm)	Load Type	Uniformly distributed imposed load (kN/m²)																																
		Span (m)																																
		0.6	0.8	1.0	1.2	1.4	1.6	1.8	2.0	2.2	2.4	2.6	2.8	3.0	3.2	3.4	3.6	3.8	4.0	4.2	4.4	4.6	4.8	5.0	5.2	5.4	5.6	5.8	6.0	6.2	6.4	6.6	6.8	7.0
40	Pressure	11.45	7.91	5.63	4.31	3.46	2.85	2.40	2.05	1.77	1.55	1.36	1.21	1.08	0.97	0.87	0.79	0.72	0.65	0.60	0.55	0.51	0.47	0.43	0.40	0.38	0.35	-	-	-	-	-	-	-
	Suction	11.11	7.51	5.27	3.98	3.16	2.59	2.17	1.85	1.59	1.39	1.22	1.08	0.96	0.86	0.78	0.70	0.64	0.58	0.53	0.49	0.45	0.42	0.39	0.36	0.34	0.31	-	-	-	-	-	-	-
53	Pressure	12.50	8.78	6.46	5.10	4.20	3.54	3.04	2.64	2.32	2.04	1.82	1.62	1.46	1.31	1.19	1.08	0.99	0.90	0.83	0.77	0.71	0.66	0.61	0.57	0.53	0.49	0.46	0.43	0.41	0.38	0.35	-	-
	Suction	12.14	8.36	6.08	4.75	3.88	3.26	2.79	2.41	2.11	1.86	1.65	1.48	1.32	1.19	1.08	0.98	0.90	0.82	0.75	0.69	0.63	0.58	0.53	0.49	0.45	0.42	0.39	0.37	0.34	0.32	0.30	-	-
60	Pressure	13.08	9.25	6.92	5.54	4.61	3.93	3.35	2.85	2.46	2.16	1.91	1.71	1.55	1.40	1.28	1.18	1.09	1.01	0.94	0.88	0.82	0.76	0.71	0.66	0.61	0.56	0.52	0.48	0.44	0.41	0.38	0.36	-
	Suction	12.70	8.83	6.53	5.18	4.28	3.63	3.08	2.61	2.25	1.97	1.75	1.57	1.41	1.28	1.17	1.08	1.00	0.92	0.83	0.76	0.69	0.63	0.58	0.54	0.50	0.46	0.43	0.40	0.38	0.35	0.33	0.31	-
73	Pressure	14.15	9.83	7.54	6.16	5.22	4.28	3.57	3.05	2.65	2.33	2.08	1.87	1.69	1.54	1.41	1.30	1.20	1.12	1.04	0.98	0.92	0.86	0.81	0.77	0.70	0.64	0.59	0.55	0.50	0.47	0.44	0.41	0.38
	Suction	13.76	9.70	7.37	5.99	4.89	3.95	3.28	2.80	2.42	2.13	1.90	1.70	1.54	1.41	1.29	1.19	1.10	1.02	0.95	0.88	0.80	0.74	0.68	0.63	0.58	0.54	0.50	0.47	0.44	0.41	0.39	0.36	0.34
80	Pressure	14.63	10.07	7.81	6.45	5.42	4.41	3.69	3.16	2.75	2.42	2.16	1.94	1.76	1.61	1.48	1.36	1.26	1.18	1.10	1.03	0.96	0.91	0.86	0.81	0.75	0.69	0.63	0.58	0.54	0.50	0.47	0.44	0.41
	Suction	14.33	10.18	7.83	6.43	5.03	4.06	3.39	2.89	2.51	2.21	1.97	1.78	1.61	1.47	1.35	1.25	1.15	1.07	1.00	0.94	0.87	0.80	0.73	0.68	0.63	0.58	0.54	0.51	0.47	0.44	0.42	0.39	0.37
91	Pressure	15.05	10.57	8.34	6.98	5.63	4.60	3.86	3.31	2.89	2.56	2.29	2.06	1.87	1.71	1.58	1.46	1.35	1.26	1.18	1.10	1.04	0.98	0.92	0.87	0.83	0.79	0.75	0.69	0.64	0.60	0.56	0.52	0.49
	Suction	15.23	10.93	8.57	6.71	5.23	4.24	3.55	3.04	2.65	2.34	2.09	1.88	1.71	1.56	1.44	1.33	1.23	1.15	1.08	1.01	0.95	0.87	0.80	0.74	0.69	0.64	0.59	0.55	0.52	0.49	0.46	0.43	0.41
100	Pressure	15.38	10.96	8.75	7.37	5.81	4.75	4.00	3.44	3.01	2.66	2.38	2.15	1.96	1.79	1.65	1.53	1.42	1.32	1.24	1.16	1.09	1.03	0.98	0.92	0.88	0.83	0.80	0.76	0.72	0.68	0.63	0.59	0.55
	Suction	15.51	11.55	9.17	6.90	5.39	4.39	3.68	3.15	2.75	2.43	2.18	1.96	1.79	1.64	1.51	1.39	1.30	1.21	1.13	1.06	1.00	0.93	0.86	0.79	0.74	0.68	0.64	0.59	0.56	0.52	0.49	0.46	0.44
115	Pressure	15.51	11.58	9.31	7.68	6.08	5.00	4.22	3.64	3.19	2.83	2.54	2.30	2.10	1.92	1.77	1.64	1.53	1.43	1.34	1.26	1.18	1.12	1.06	1.00	0.95	0.91	0.87	0.83	0.79	0.76	0.73	0.70	0.67
	Suction	15.51	11.63	9.31	7.20	5.65	4.62	3.88	3.34	2.92	2.59	2.32	2.10	1.91	1.75	1.62	1.50	1.39	1.30	1.22	1.15	1.08	1.02	0.95	0.88	0.82	0.76	0.71	0.66	0.62	0.58	0.54	0.51	0.48
120	Pressure	15.51	11.63	9.31	7.76	6.17	5.08	4.30	3.71	3.25	2.89	2.59	2.35	2.14	1.96	1.81	1.68	1.56	1.46	1.37	1.29	1.21	1.15	1.09	1.03	0.98	0.93	0.89	0.85	0.81	0.78	0.75	0.72	0.69
	Suction	15.51	11.63	9.31	7.30	5.74	4.70	3.95	3.40	2.97	2.64	2.36	2.14	1.95	1.79	1.65	1.53	1.43	1.33	1.25	1.17	1.11	1.05	0.98	0.91	0.84	0.78	0.73	0.68	0.64	0.60	0.56	0.53	0.50
137	Pressure	15.51	11.63	9.31	7.76	6.47	5.35	4.53	3.92	3.45	3.07	2.76	2.50	2.28	2.10	1.94	1.80	1.68	1.57	1.47	1.38	1.31	1.24	1.17	1.11	1.06	1.01	0.96	0.92	0.88	0.84	0.81	0.78	0.75
	Suction	15.51	11.63	9.31	7.63	6.03	4.95	4.17	3.60	3.15	2.80	2.51	2.28	2.08	1.91	1.76	1.64	1.53	1.43	1.34	1.26	1.19	1.13	1.07	1.00	0.92	0.86	0.80	0.75	0.70	0.66	0.62	0.58	0.55
150	Pressure	15.51	11.63	9.31	7.76	6.65	5.54	4.71	4.08	3.59	3.20	2.88	2.61	2.39	2.19	2.03	1.88	1.76	1.65	1.54	1.45	1.37	1.30	1.23	1.17	1.12	1.06	1.02	0.97	0.93	0.89	0.86	0.82	0.79
	Suction	15.51	11.63	9.31	7.73	6.24	5.13	4.34	3.74	3.28	2.92	2.62	2.38	2.17	2.00	1.85	1.72	1.60	1.50	1.41	1.33	1.25	1.19	1.13	1.06	0.99	0.92	0.85	0.80	0.75	0.70	0.66	0.62	0.58
167	Pressure	15.51	11.63	9.31	7.76	6.65	5.79	4.93	4.28	3.77	3.36	3.03	2.75	2.52	2.32	2.14	1.99	1.86	1.74	1.64	1.54	1.46	1.38	1.31	1.25	1.19	1.13	1.08	1.04	0.99	0.95	0.92	0.88	0.85
	Suction	15.51	11.63	9.30	7.72	6.51	5.37	4.55	3.93	3.45	3.07	2.76	2.51	2.29	2.11	1.95	1.81	1.69	1.59	1.49	1.41	1.33	1.26	1.20	1.14	1.06	0.99	0.92	0.86	0.80	0.75	0.71	0.67	0.63

- Values have been calculated using the method described in BS EN 14509: 2013, for dark coloured panels.
- The following deflection limits have been used:
 - Short term pressure loading $L/100$.
 - Short term suction loading $L/100$.
- All panel thicknesses have been calculated with a minimum end support width of 50 mm and intermediate support width of 50 mm. Larger support widths are possible.

- The actual wind suction resisted by the panel is dependent upon the number of fasteners and the material of the supporting element.
- The fastener calculation should be carried out in accordance with the appropriate standards.
- For intermediate values linear interpolation may be used.
- The allowable steelwork tolerance between bearing planes of adjacent supports is ± 5 mm.

Contact Details

UK

Kingspan Limited

Greenfield Business Park No. 2
Greenfield | Holywell | Flintshire
North Wales | CH8 7GJ

T: +44 (0) 1352 716100

E: info@kingspanpanels.com

www.kingspanpanels.co.uk



Ireland

Kingspan Limited

Carrickmacross Road | Kingscourt
Co. Cavan | A82 E897

T: +353 (0) 42 96 98500

E: info.ire@kingspanpanels.com

www.kingspanpanels.ie



Please scan for the most up to date version of this document.

For the product offering in other markets please contact your local sales representative or visit www.kingspanpanels.com

Care has been taken to ensure that the contents of this publication are accurate, but Kingspan Limited and its subsidiary companies do not accept responsibility for errors or for information that is found to be misleading. Suggestions for, or description of, the end use or application of products or methods of working are for information only and Kingspan Limited and its subsidiaries accept no liability in respect thereof.

